

Softflex® 0826

Thermoplastic Elastomer

Network Polymers, Inc.

Message:

Softflex 0826 is suitable for overmolding ABS, PC, ABS/PC and PPO.

General Information			
Forms	Pellets		
Processing Method	Coating Injection Molding		
Physical	Nominal Value	Unit	Test Method
Specific Gravity	0.952	g/cm ³	ASTM D792
Melt Mass-Flow Rate (MFR)			ASTM D1238
200°C/5.0 kg ¹	8.5	g/10 min	
235°C/1.0 kg	8.0	g/10 min	
Hardness	Nominal Value	Unit	Test Method
Durometer Hardness			ASTM D2240
Shore A	44 to 50		
Shore A, 10 sec	38 to 44		
Mechanical	Nominal Value	Unit	Test Method
Flexural Modulus	5.65	MPa	ASTM D790
Taber Abrasion Resistance (1000 Cycles, 1000 g, H-22 Wheel)	44.0	mg	ASTM D3389
Elastomers	Nominal Value	Unit	Test Method
Tensile Set (100% Strain)	7	%	ASTM D412
Tensile Stress			ASTM D412
50% Strain	0.834	MPa	
100% Strain	1.23	MPa	
300% Strain	2.22	MPa	
Tensile Strength (Yield)	7.11	MPa	ASTM D412
Tensile Elongation (Break)	740	%	ASTM D412
Tear Strength	25.4	kN/m	ASTM D624
Impact	Nominal Value	Unit	Test Method
Gardner Impact (-30°C)	> 36.2	J	ASTM D5420
Injection	Nominal Value	Unit	
Drying Temperature	54.4 to 60.0	°C	
Drying Time	4.0 to 6.0	hr	
Suggested Shot Size	40 to 80	%	
Rear Temperature	160 to 182	°C	

Middle Temperature	171 to 193	°C
Front Temperature	210 to 221	°C
Nozzle Temperature	199 to 216	°C
Processing (Melt) Temp	193 to 210	°C
Mold Temperature	26.7 to 48.9	°C
Injection Pressure	34.5 to 41.4	MPa
Holding Pressure	27.6 to 31.0	MPa
Back Pressure	0.517 to 1.03	MPa
Screw Speed	20 to 40	rpm

NOTE

1. Procedure A

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

Recommended distributors for this material

Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533

Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

