

Monprene® CP-18240 (PRELIMINARY DATA)

Thermoplastic Elastomer

Teknor Apex Company

Message:

The Monprene CP-18200 Unfilled, High Flow Series of thermoplastic elastomer compounds, with good UV resistance, available in NAT or colors, from 40 to 80 Shore A, are designed specifically for EU consumer product applications requiring a soft, rubber-like feel. Monprene CP-18240 is a low hardness, low density grade that is suitable for injection molding.

| General Information | |
|---------------------|----------------------------------|
| Features | Low Specific Gravity |
| | Without Fillers |
| | Low density |
| | Good UV resistance |
| | Good formability |
| | Good flexibility |
| | Good coloring |
| | Good adhesion |
| | High liquidity |
| | Good chemical resistance |
| | Good toughness |
| | Hardness, low |
| | |
| Uses | Handle |
| | overmolding |
| | Plug |
| | Bushing |
| | Washer |
| | Washer |
| | Leather case |
| | Soft touch application |
| | Soft handle |
| | General |
| | Rubber substitution |
| | Consumer goods application field |
| | Knob |
| | |
| RoHS Compliance | RoHS compliance |
| Appearance | Translucent |
| | Available colors |
| | |
| Forms | Particle |

| | | | |
|--|-------------------|-------------------|-------------|
| Processing Method | Injection molding | | |
| Physical | Nominal Value | Unit | Test Method |
| Density | 0.890 | g/cm ³ | ISO 1183 |
| Hardness | Nominal Value | Unit | Test Method |
| Durometer Hardness (Shore A, 5 sec) | 40 | | ISO 868 |
| Elastomers | Nominal Value | Unit | Test Method |
| Tensile Stress | | | ISO 37 |
| 100% strain | 1.10 | MPa | ISO 37 |
| 300% strain | 1.70 | MPa | ISO 37 |
| Tensile Strength (Break) | 7.80 | MPa | ISO 37 |
| Tensile Elongation (Break) | 900 | % | ISO 37 |
| Compression Set | | | ISO 815 |
| 23°C, 22 hr | 22 | % | ISO 815 |
| 70°C, 22 hr | 44 | % | ISO 815 |
| Fill Analysis | Nominal Value | Unit | Test Method |
| Apparent Viscosity (200°C, 206 sec ⁻¹) | 101 | Pa · s | ISO 11443 |

Legal statement

The information and recommendations contained in this bulletin are, to the best of our knowledge, accurate and reliable but no guarantee of their accuracy is made. All products are sold upon condition that purchasers shall make their own tests to determine the suitability of such products for their particular purposes and uses and purchaser assumes all risks and liability for the results of use of the products, including use in accordance with seller's recommendations. Nothing in this bulletin constitutes permission or a recommendation to practice or use any invention covered by any patent owned by this company or others. There is no warranty of merchantability and there are no other warranties for the products described. For detailed Product Stewardship information, please contact us. Any product of Teknor Apex, including product names, shall not be used or tested in medical or food contact applications without the prior written acknowledgement of Teknor Apex as to the intended use. Please note that some products may not be available in one or more countries.

| | | |
|------------------------|---------------|------|
| Injection | Nominal Value | Unit |
| Rear Temperature | 120 - 160 | °C |
| Middle Temperature | 160 - 230 | °C |
| Front Temperature | 180 - 230 | °C |
| Nozzle Temperature | 180 - 230 | °C |
| Processing (Melt) Temp | 180 - 230 | °C |
| Mold Temperature | 15 - 50 | °C |
| Injection Rate | Fast | |
| Back Pressure | 0.500 - 1.50 | MPa |
| Screw Speed | 50 - 100 | rpm |
| Cushion | 3.00 - 25.0 | mm |

Injection instructions

Drying is not necessary. However, if moisture is a problem, dry the pellets for 2 to 4 hours at 65°C (150°F). Low holding pressure is recommended

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

Recommended distributors for this material

Susheng Import & Export Trading Co., Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533

Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

