

Makrolon® 2558

Polycarbonate

Covestro - Polycarbonates

Message:

MVR (300 °C/1.2 kg) 14 cm³/10 min; medical devices; suitable for ETO and steam sterilization at 121 °C; biocompatible according to many ISO 10993-1 test requirements; medium viscosity; easy release; injection molding - melt temperature 280 - 320 °C; available in transparent and opaque colors

General Information			
UL YellowCard	E41613-101010217		
Features	Biocompatible		
	Ethylene Oxide Sterilizable		
	Good Mold Release		
	Medium Viscosity		
	Steam Sterilizable		
Uses	Medical Devices		
	Medical/Healthcare Applications		
Agency Ratings	ISO 10993-Part 1		
RoHS Compliance	RoHS Compliant		
Appearance	Clear/Transparent		
	Colors Available		
	Opaque		
Processing Method	Injection Molding		
Physical	Nominal Value	Unit	Test Method
Density (23°C)	1.20	g/cm ³	ISO 1183
Apparent Density ¹	0.66	g/cm ³	ISO 60
Melt Mass-Flow Rate (MFR) (300°C/1.2 kg)	16	g/10 min	ISO 1133
Melt Volume-Flow Rate (MVR) (300°C/1.2 kg)	14.0	cm ³ /10min	ISO 1133
Molding Shrinkage			
Across Flow	0.60 to 0.80	%	ISO 2577
Flow	0.60 to 0.80	%	ISO 2577
Across Flow : 2.00 mm ²	0.70	%	ISO 294-4
Flow : 2.00 mm ³	0.65	%	ISO 294-4
Water Absorption			ISO 62
Saturation, 23°C	0.30	%	
Equilibrium, 23°C, 50% RH	0.12	%	
Hardness	Nominal Value	Unit	Test Method
Ball Indentation Hardness	115	MPa	ISO 2039-1

Mechanical	Nominal Value	Unit	Test Method
Tensile Modulus (23°C)	2400	MPa	ISO 527-2/1
Tensile Stress			ISO 527-2/50
Yield, 23°C	66.0	MPa	
Break, 23°C	70.0	MPa	
Tensile Strain			ISO 527-2/50
Yield, 23°C	6.1	%	
Break, 23°C	130	%	
Nominal Tensile Strain at Break (23°C)	> 50	%	ISO 527-2/50
Tensile Creep Modulus			ISO 899-1
1 hr	2200	MPa	
1000 hr	1900	MPa	
Flexural Modulus ⁴ (23°C)	2400	MPa	ISO 178
Flexural Stress ⁵			ISO 178
3.5% Strain, 23°C	73.0	MPa	
23°C	97.0	MPa	
Flexural Strain at Flexural Strength ⁶ (23°C)	7.1	%	ISO 178
Flash Ignition Temperature	480	°C	ASTM D1929
Self Ignition Temperature	550	°C	ASTM D1929
ISO Shortname	ISO 7391-PC,MR,(,,)-18-9		
Impact	Nominal Value	Unit	Test Method
Charpy Notched Impact Strength ⁷			ISO 7391
-30°C, Complete Break	16	kJ/m ²	
23°C, Partial Break	70	kJ/m ²	
Charpy Unnotched Impact Strength			ISO 179/1eU
-60°C	No Break		
-30°C	No Break		
23°C	No Break		
Notched Izod Impact Strength ⁸			ISO 7391
-30°C, Complete Break	15	kJ/m ²	
23°C, Partial Break	65	kJ/m ²	
Multi-Axial Instrumented Impact Energy			ISO 6603-2
-30°C	65.0	J	
23°C	60.0	J	
Multi-Axial Instrumented Impact Peak Force			ISO 6603-2
-30°C	6300	N	
23°C	5400	N	
Thermal	Nominal Value	Unit	Test Method
Heat Deflection Temperature			
0.45 MPa, Unannealed	136	°C	ISO 75-2/B
1.8 MPa, Unannealed	124	°C	ISO 75-2/A

Glass Transition Temperature ⁹	144	°C	ISO 11357-2
Vicat Softening Temperature			
--	144	°C	ISO 306/B50
--	145	°C	ISO 306/B120
Ball Pressure Test (138°C)	Pass		IEC 60695-10-2
CLTE			ISO 11359-2
Flow : 23 to 55°C	6.5E-5	cm/cm/°C	
Transverse : 23 to 55°C	6.5E-5	cm/cm/°C	
Thermal Conductivity ¹⁰ (23°C)	0.20	W/m/K	ISO 8302
Electrical	Nominal Value	Unit	Test Method
Surface Resistivity	1.0E+16	ohms	IEC 60093
Volume Resistivity (23°C)	1.0E+16	ohms·cm	IEC 60093
Electric Strength (23°C, 1.00 mm)	34	kV/mm	IEC 60243-1
Relative Permittivity			IEC 60250
23°C, 100 Hz	3.10		
23°C, 1 MHz	3.00		
Dissipation Factor			IEC 60250
23°C, 100 Hz	5.0E-4		
23°C, 1 MHz	9.0E-3		
Comparative Tracking Index (Solution A)	250	V	IEC 60112
Flammability	Nominal Value	Unit	Test Method
Oxygen Index ¹¹	28	%	ISO 4589-2
Optical	Nominal Value	Unit	Test Method
Refractive Index ¹²	1.586		ISO 489
Transmittance			ISO 13468-2
1000 µm	89.0	%	
2000 µm	89.0	%	
3000 µm	88.0	%	
4000 µm	87.0	%	
Haze (3000 µm)	< 0.80	%	ISO 14782
NOTE			
1.	Pellets		
2.	60x60x2 mm, 500 bar		
3.	60x60x2 mm, 500 bar		
4.	2.0 mm/min		
5.	2.0 mm/min		
6.	2 mm/min		
7.	Based on ISO 179-1eA, 3 mm		
8.	Based on ISO 180-A, 3 mm		
9.	10°C/min		
10.	Cross-flow		
11.	Procedure A		

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

Recommended distributors for this material

Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533

Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

