Petrothene® GA502023

Linear Low Density Polyethylene

LyondellBasell Industries

Message:

The Petrothene GA502 series of resins are pelletized linear low density polyethylenes for applications requiring excellent drawdown and toughness. These pelletized products offer excellent additive homogeneity, require no transfer equipment modification and facilitate clean and safe storage and handling. They can be used in either blown or cast film extrusion.

General Information			
Additive	Antiblock (5500 ppm)		
	Slip (900 ppm)		
Features	Antiblocking		
	Food Contact Acceptable		
	Good Drawdown		
	Good Toughness		
	Slip		
Uses	Cast Film		
	Film		
Agency Ratings	FDA 21 CFR 177.1520		
Forms	Pellets		
Processing Method	Blown Film		
	Cast Film		
	Film Extrusion		
Physical	Nominal Value	Unit	Test Method
Density	0.918	g/cm³	ASTM D1505
Melt Mass-Flow Rate (MFR) (190°C/2.16			
kg)	2.0	g/10 min	ASTM D1238
Films	Nominal Value	Unit	Test Method
Film Thickness - Tested	38	μm	
Secant Modulus			ASTM D882
1% Secant, MD : 38 µm	221	MPa	
1% Secant, TD : 38 µm	248	MPa	
Tensile Strength			ASTM D882
MD : Break, 38 µm	33.8	MPa	
TD : Break, 38 µm	24.8	MPa	
Tensile Elongation			ASTM D882
MD : Break, 38 µm	750	%	

TD : Break, 38 μm	800	%	
Dart Drop Impact (38 µm, Blown Film)	120	g	ASTM D1709A
Elmendorf Tear Strength			ASTM D1922
MD : 38 µm	170	g	
TD : 38 μm	400	g	
Optical	Nominal Value	Unit	Test Method
Optical Gloss (45°, 38.1 µm, Blown Film)	Nominal Value 60	Unit	Test Method ASTM D2457
		Unit %	
Gloss (45°, 38.1 μm, Blown Film)	60		ASTM D2457

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

Recommended distributors for this material

Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533

Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

