Milastomer™ W700B

Thermoplastic Vulcanizate

Mitsui Chemicals America, Inc.

Message:

Milastomer™W700B is a thermoplastic vulcanized rubber (TPV) material. This product is available in North America and is processed by blow molding or extrusion.

Milastomer™The typical application areas of W700B are: engineering/industrial accessories

| General Information | | | |
|--|---------------------------------|----------|-----------------|
| Uses | Washer | | |
| | Weather-resistant sealing strip | | |
| Appearance | Black | | |
| Forms | Particle | | |
| Processing Method | Blow molding | | |
| | Extrusion | | |
| Physical | Nominal Value | Unit | Test Method |
| Density | 0.880 | g/cm³ | ASTM D1505 |
| Melt Mass-Flow Rate (MFR) (230°C/10 kg) | 0.0 30 | g/10 min | ISO 1133 |
| Hardness | Nominal Value | Unit | Test Method |
| Durometer Hardness | | | ISO 48 |
| Shaw A | 73 | | ISO 48 |
| Shaw A, 5 seconds | 67 | | ISO 48 |
| Elastomers | Nominal Value | Unit | Test Method |
| Tensile Stress ¹ (100% Strain) | 2.50 | МРа | ISO 37 |
| Tensile Stress ² (Break) | 5.60 | МРа | ISO 37 |
| Tensile Elongation ³ (Break) | 450 | % | ISO 37 |
| Compression Set | | | ISO 815 |
| 23°C, 22 hr | 29 | % | ISO 815 |
| 70°C, 22 hr | 45 | % | ISO 815 |
| Thermal | Nominal Value | Unit | Test Method |
| Brittleness Temperature | < -60.0 | °C | Internal method |
| Additional Information | | | |
| All tests performed according to Mits | ui methods. | | |
| NOTE | | | |
| 1. | 500 mm/min | | |
| 2. | 500 mm/min | | |
| 3. | 500 mm/min | | |

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

Recommended distributors for this material

Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533 Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

