

LUVOCOM® 19/CF/30/MS/2

Polyamide 46
Lehmann & Voss & Co.

Message:

LUVOCOM® 19/CF/30/MS/2 is a polyamide 46 (nylon 46) material, which contains a 30% carbon fiber reinforced material. This product is available in Europe.

LUVOCOM®The main features of 19/CF/30/MS/2 are:

Conductivity

High stiffness

high strength

Electrostatic protection

Lubrication

Typical application areas include:

engineering/industrial accessories

textile/fiber

Automotive Industry

business/office supplies

General Information			
Filler / Reinforcement	Carbon fiber reinforced material, 30% filler by weight		
Additive	Lubricant		
Features	Conductivity		
	Rigidity, high		
	High strength		
	Electrostatic discharge protection		
	Lubrication		
Uses	Gear		
	Textile applications		
	Engineering accessories		
	Application in Automobile Field		
	Business equipment		
	Cam		
Appearance	Natural color		
Physical	Nominal Value	Unit	Test Method
Density	1.31	g/cm³	ISO 1183
Molding Shrinkage	0.050 - 0.30	%	DIN 16901
Water Absorption (23°C, 24 hr)	< 1.0	%	
Mechanical	Nominal Value	Unit	Test Method
Tensile Modulus	24000	MPa	ISO 527-2
Tensile Stress (Break)	275	MPa	ISO 527-2
Tensile Strain (Yield)	1.7	%	ISO 527-2
Flexural Modulus	21000	MPa	ISO 178

Flexural Stress	395	MPa	ISO 178
Flexural Strain at Flexural Strength	1.9	%	ISO 178
Maximum operating temperature-Short Term	160	°C	
Insulation Resistance		ohms	IEC 60167
Impact	Nominal Value	Unit	Test Method
Charpy Notched Impact Strength (23°C)	8.0	kJ/m ²	ISO 179/1eA
Charpy Unnotched Impact Strength (23°C)	60	kJ/m ²	ISO 179/1eU
Thermal	Nominal Value	Unit	Test Method
Continuous Use Temperature	150	°C	UL 746B
CLTE - Flow	2.0E-5	cm/cm/°C	DIN 53752
Thermal Conductivity	0.35	W/m/K	DIN 52612
Electrical	Nominal Value	Unit	Test Method
Surface Resistivity	< 1.0E+3	ohms	IEC 60093
Injection	Nominal Value	Unit	
Drying Temperature			
A	80.0	°C	
Vacuum dryer, B	80.0	°C	
Drying Time			
A	2.0 - 8.0	hr	
Vacuum dryer, B	2.0 - 12	hr	
Suggested Max Moisture	0.10	%	
Rear Temperature	285 - 315	°C	
Middle Temperature	305 - 315	°C	
Front Temperature	305 - 315	°C	
Nozzle Temperature	280 - 330	°C	
Processing (Melt) Temp	310	°C	
Mold Temperature	120 - 140	°C	
Injection instructions			

General

In general LUVOCOM® can be processed on conventional injection moulding machines while observing the usual technical guidelines.

Any added fibrous materials or fillers may have an abrasive effect. In this case the cylinder and screw should be protected against wear as is usual in the processing of reinforced thermoplastic materials.

Lengthy dwell times for the melts in the cylinder should be avoided.

Lower the temperatures during interruptions!

Predrying (optional)

It is advisable to predry the granulate with a suitable dryer immediately before processing.

The granulate may absorb moisture from the air.

Delivery Form & Storage

Unless indicated otherwise, the material is delivered as 3mm-long pellets in sealed bags on pallets.

Preferably storage should be effected in dry and normally temperatured rooms

Additional Information

During processing the moisture level should not exceed 0.1%, otherwise molecular degradation and surface defects (e.g. smearing) may occur. As the material absorbs water very rapidly, originally sealed containers should only be opened immediately before processing. Excessively high predrying temperatures may cause discoloration.

The processing notes provided merely represent a recommendation for general use. Due to the large variety of machines, geometries and volumes of parts, etc., it may be necessary to employ different settings according to the specific application.

Please contact us for further information.

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection.All rights belong to the original authors. If any infringement occurs, please contact us immediately.

Recommended distributors for this material

Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519
Phone: +86 13424755533
Email: sales@su-jiao.com
No. 215, Lianhe North Road, Fengxian District, Shanghai, China

