LUVOCOM® 19-7950 VP

Polyamide 46

Lehmann & Voss & Co.

Message:

LUVOCOM® 19-7950 VP is a polyamide 46 (nylon 46) material containing aramid fibers. This product is available in North America, Africa and the Middle East, Latin America, Europe or Asia Pacific. LUVOCOM®The main characteristics of 19-7950 VP are: lubrication.

Typical application areas include:

engineering/industrial accessories

Electrical/electronic applications

textile/fiber

Automotive Industry

business/office supplies

General Information

Filler / Reinforcement	Aramid fiber			
Additive	PTFE lubricant			
Features	Good liquidity			
	Lubrication			
Uses	Gear			
	Textile applications			
	Engineering accessories			
	Switch			
	Application in Automobile Field			
	Business equipment			
	Bearing			
Appearance	Natural color			
Physical	Nominal Value	Unit	Test Method	
Density	1.25	g/cm³	ISO 1183	
Molding Shrinkage	1.2 - 1.9	%	DIN 16901	
Water Absorption (23°C, 24 hr)	< 1.0	%		
Mechanical	Nominal Value	Unit	Test Method	
Tensile Modulus	3300	MPa	ISO 527-2	
Tensile Stress (Break)	75.0	MPa	ISO 527-2	
Tensile Strain (Yield)	8.0	%	ISO 527-2	
Flexural Modulus	2800	MPa	ISO 178	
Flexural Stress	105	MPa	ISO 178	
Flexural Strain at Flexural Strength	10	%	ISO 178	
Maximum operating temperature-Short				
Term	160	°C		
Insulation Resistance	> 1.0E+12	ohms	IEC 60167	
Impact	Nominal Value	Unit	Test Method	

Charpy Notched Impact Strength (23°C)	5.0	kJ/m²	ISO 179/1eA
Charpy Unnotched Impact Strength (23°C)	45	kJ/m²	ISO 179/1eU
Thermal	Nominal Value	Unit	Test Method
Continuous Use Temperature	150	°C	UL 746B
Electrical	Nominal Value	Unit	Test Method
Surface Resistivity	> 1.0E+12	ohms	IEC 60093
Injection	Nominal Value	Unit	
Drying Temperature			
A	80.0	°C	
Vacuum dryer, B	80.0	°C	
Drying Time			
A	2.0 - 8.0	hr	
Vacuum dryer, B	2.0 - 12	hr	
Suggested Max Moisture	0.10	%	
Rear Temperature	285 - 315	°C	
Middle Temperature	305 - 315	°C	
Front Temperature	305 - 315	°C	
Nozzle Temperature	280 - 330	°C	
Processing (Melt) Temp	310	°C	
Mold Temperature	120 - 140	°C	
Injection instructions			

General

In general LUVOCOM® can be processed on conventional injection moulding machines while observing the usual technical guidelines.

Any added fibrous materials or fillers may have an abrasive effect. In this case the cylinder and screw should be protected against wear as is usual in the processing of reinforced thermoplastic materials.

Lengthy dwell times for the melts in the cylinder should be avoided.

Lower the temperatures during interruptions!

Predrying (optional)

It is advisable to predry the granulate with a suitable dryer immediately before processing.

The granulate may absorb moisture from the air.

Delivery Form & Storage

Unless indicated otherwise, the material is delivered as 3mm-long pellets in sealed bags on pallets.

Preferably storage should be effected in dry and normally temperatured rooms

Additional Information

During processing the moisture level should not exceed 0.1%, otherwise molecular degradation and surface defects (e.g. smearing) may occur. As the material absorbs water very rapidly, originally sealed containers should only be opened immediately before processing. Excessively high predrying temperatures may cause discoloration.

The processing notes provided merely represent a recommendation for general use. Due to the large variety of machines, geometries and volumes of parts, etc., it may be necessary to employ different settings according to the specific application.

Please contact us for further information.

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

Recommended distributors for this material

Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533

Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

