# **AVALON® 65 DB**

## Thermoplastic Polyurethane Elastomer (Polyester)

## **Huntsman Corporation**

### Message:

AVALON 65 DB is a high performance polyester based thermoplastic polyurethane for injection moulding.

AVALON 65 DB is part of the AVALON Perform Range and offers a premium soling material for sports footwear and top-pieces.

The features offered include:

Durability

Excellent surface definition

Abrasion resistance

Flex resistance

Phthalate free TPU

General Information				
Features	Good wear resistance			
	Durability			
	Excellent appearance			
Uses	Sporting goods			
	Footwear			
Forms	Particle			
Processing Method	Injection molding			
Physical	Nominal Value	Unit	Test Method	
Density	1.23	g/cm³	ISO 2781	
Hardness	Nominal Value	Unit	Test Method	
Durometer Hardness (Shore D)	65		ISO 868	
Mechanical	Nominal Value	Unit	Test Method	
Flexural Modulus (23°C)	250	MPa	ISO 178	
Abrasion Resistance	35.0	mm³	ISO 4649	
Elastomers	Nominal Value	Unit	Test Method	
Tensile Stress			ISO 37	
100% strain	22.0	MPa	ISO 37	
300% strain	34.0	MPa	ISO 37	
Tensile Stress (Break)	45.0	MPa	ISO 37	
Tensile Elongation (Break)	350	%	ISO 37	
Tear Strength <sup>1</sup>	220	kN/m	ISO 34-1	
Compression Set (23°C)	25	%	ISO 815	
Additional Information				
Test plates conditioned 20 hours at 100°0	C before testing			
Injection	Nominal Value	Unit		
Drying Temperature - Desiccant Dryer	80.0 - 90.0	°C		

Drying Time - Desiccant Dryer	2.0	hr	
Hopper Temperature	25.0 - 35.0	°C	
Rear Temperature	190 - 210	°C	
Middle Temperature	195 - 215	°C	
Front Temperature	200 - 220	°C	
Nozzle Temperature	195 - 210	°C	
Mold Temperature	25.0 - 50.0	°C	
Injection Pressure	2.00 - 10.0	MPa	
Injection Rate	Slow		
Holding Pressure	1.00 - 5.00	MPa	
Back Pressure	0.0300 - 0.300	MPa	
Screw Speed	20 - 80	rpm	
Screw L/D Ratio	20.0:1.0 to 25.0:1.0		
Screw Compression Ratio	2.0 : 1.0 - 3.0 : 1.0		
	<u> </u>	·	

#### Injection instructions

Typical Screw Diameter: 40 - 120 mm3 Stage Design

Feed Zone : 0.4L Compression Zone : 0.3L Metering Zone : 0.3L

#### NOTE

1.

Method B, right-angle specimen

(without cut)

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

## Recommended distributors for this material

## Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533 Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

