

# Virantage® VW-10200 RP, RFP, RSFP

Polyethersulfone

Solvay Specialty Polymers

Message:

Virantage® VW-series functionalized polyethersulfones (r-PESU) are amorphous, high-temperature sulfone polymers featuring reactive end groups to enhance solubility and improve interfacial properties in epoxy thermosets. Their inherent toughness imparts damage tolerance to thermoset composites and excellent flexibility to coatings. Virantage® polymers also offer superior thermal and hydrolytic stability that delivers best-in-class hot-wet performance.

They are especially suitable for incorporation into advanced composite resin systems used to produce high-performance aerospace components and have been used successfully in a variety of thermosetting resin systems including epoxies, phenolics, and BMIs.

Virantage® VW-series polymers are available in a range of molecular weights: high (10200), medium (10300) and low (10700). A range of particle sizes is also available to meet formulators' specific needs.

All Virantage® PESU polymers are produced at Solvay's state-of-the-art, world-scale facility in Panoli, India under ISO 9001:2000 and ISO 14001:2004 certified quality management systems.

General Information			
Features	Amorphous		
	Good Thermal Stability		
	Good Toughness		
	High Heat Resistance		
	High Molecular Weight		
	High Viscosity		
	Hydrolytically Stable		
Uses	Aerospace Applications		
RoHS Compliance	Contact Manufacturer		
Forms	Pellets		
Processing Method	Coating		
	Compounding		
Physical	Nominal Value	Unit	Test Method
Solution Viscosity <sup>1</sup>	800	mPa · s	Internal Method
Average Molecular Weight <sup>2</sup>	46500	g/mol	Internal Method
Moisture - Measured at time of packaging <sup>3</sup>	1.5	%	Internal Method
OH End Groups - Measured by titration of end groups	75	µeq/g	Internal Method
Particle Size <sup>4</sup>			
VW-10200RFP	63.0	µm	
VW-10200RP	500	µm	
VW-10200RSFP	38.0	µm	
Residual Solvent - Measured by Gas Chromatography	0.15	%	Internal Method
Thermal	Nominal Value	Unit	Test Method

Glass Transition Temperature	220	°C	DSC
NOTE			
1.	25% solution in DMAc at 40°C		
2.	Gel Permeation Chromatography with polystyrene as standard		
3.	Virantage® r-PESU is hygroscopic and may absorb moisture in storage. Dry no higher than 130°C for a minimum of 3 hours if needed.		
4.	Typical Particle Size ~D90 Particle sizes by sieve measurement		

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

#### Recommended distributors for this material

### Susheng Import & Export Trading Co., Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533

Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

