

# STERalloy™ FDG 2036-5

Thermoplastic

Hapco Inc.

## Message:

STERalloy FDG is the first Liquid Molding Polymer Alloy Series that has been specifically designed for food and drug applications. All of the products in the STERalloy FDG Series exhibit unique physical and chemical properties and have been used in numerous applications where biocompatibility is required.

Key Advantages:

Approvable Materials

Wide range of hardnesses

ROHS compliant

Very high physical properties

Low moisture sensitivity

Easy to use

The food, drug, pharmaceutical, wine, beer, juice, dairy, hospital equipment, and prosthetic industries are just some examples of applications that utilize special products such as STERalloy FDG.

STERalloy FDG Elastomeric Series:

various hardness elastomers, shore 20A - 72D

clear in color

available in 2 speeds - fast and slow

STERalloy FDG Rigid Series:

rigid, tough polymer alloy plastics

high heat distortion

high physical properties

General Information			
Features	Food Contact Acceptable		
	Good Processability		
Uses	Filtration Media		
	Food Containers		
	Medical/Healthcare Applications		
	Non-specific Food Applications		
	Pharmaceuticals		
	Prosthetics		
RoHS Compliance	RoHS Compliant		
Appearance	Clear/Transparent		
Forms	Liquid		
Physical	Nominal Value	Unit	Test Method
Specific Gravity	1.16	g/cm <sup>3</sup>	ASTM D4669
Molding Shrinkage - Flow	0.20 to 0.40	%	ASTM D2566
Weight - per cubic inch	19	g	
Gel Time <sup>1</sup> (25°C)	4.0 to 6.0	min	ASTM D2971
Hardness	Nominal Value	Unit	Test Method
Durometer Hardness (Shore A)	30 to 40		ASTM D2240

Mechanical	Nominal Value	Unit	Test Method
Tensile Strength	3.10	MPa	ASTM D638
Tensile Elongation (Break)	1000	%	ASTM D638
Elastomers	Nominal Value	Unit	Test Method
Tear Strength <sup>2</sup>	14.9	kN/m	ASTM D624
Impact	Nominal Value	Unit	Test Method
Notched Izod Impact	No Break		ASTM D256
Unnotched Izod Impact	No Break		ASTM D256
Thermoset	Nominal Value	Unit	Test Method
Thermoset Components			
Part A	Mix Ratio by Weight: 100, Mix Ratio by Volume: 100		
Part B	Mix Ratio by Weight: 300, Mix Ratio by Volume: 300		
Thermoset Mix Viscosity (25°C)	3000	cP	ASTM D4878
Demold Time (21°C)	120 to 240	min	Internal Method
NOTE			
1.	100 g		
2.	Die C		

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

#### Recommended distributors for this material

### Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533

Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

