

Complet® LGF50-PA66

Polyamide 66

PlastiComp, Inc.

Message:

Complet® LGF50-PA66 is a polyamide 66 (nylon 66) product, which contains 50% long glass fibers as filler. It is available in North America, Europe or Asia Pacific. The main features are: Rohs certification.

General Information			
Filler / Reinforcement	Long glass fiber, 50% filler by weight		
RoHS Compliance	RoHS compliance		
Forms	Particle		
Physical	Nominal Value	Unit	Test Method
Specific Gravity	1.60	g/cm ³	ASTM D792
Mechanical	Nominal Value	Unit	Test Method
Tensile Modulus	17200	MPa	ASTM D638
Tensile Strength	265	MPa	ASTM D638
Tensile Elongation (Break)	1.0 - 2.0	%	ASTM D638
Flexural Modulus	16500	MPa	ASTM D790
Flexural Strength	369	MPa	ASTM D790
Impact	Nominal Value	Unit	Test Method
Notched Izod Impact	430	J/m	ASTM D256
Unnotched Izod Impact	1400	J/m	ASTM D4812
Thermal	Nominal Value	Unit	Test Method
Deflection Temperature Under Load (1.8 MPa, Unannealed)	254	°C	ASTM D648
Injection	Nominal Value	Unit	
Drying Temperature	85.0	°C	
Drying Time	4.0	hr	
Suggested Max Moisture	0.18	%	
Suggested Max Regrind	5	%	
Rear Temperature	282 - 299	°C	
Middle Temperature	288 - 304	°C	
Front Temperature	293 - 310	°C	
Nozzle Temperature	288 - 304	°C	
Processing (Melt) Temp	293 - 310	°C	
Mold Temperature	93.3	°C	
Back Pressure	0.172 - 0.345	MPa	
Screw Speed	30 - 50	rpm	
Cushion	6.35	mm	
Screw L/D Ratio	18.0:1.0 to 20.0:1.0		
Screw Compression Ratio	2.0 : 1.0 - 3.0 : 1.0		

Injection instructions

Injection speed: 2 to 3 in/sec Injection pressure: medium to maximum

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

Recommended distributors for this material

Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533

Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

