Vipel® F085-BBB-00

Vinyl Ester

AOC, L.L.C.

Message:

Vipel Corrosion Resistant Epoxy Novolac, Vinyl Ester Resin

The Vipel F085 series is an epoxy novolac vinyl ester resin dissolved in styrene. The Vipel F085 series is ideally suited for applications where outstanding mechanical properties and resistance to chemicals, oxidation and heat are required.

Corrosion resistance

The epoxy novolac backbone chemistry provides resistance to acids and bases and has superior resistance to many organic solvents. Vipel F085 series is generally resistant to liquids and vapors at higher temperatures than standard bisphenol-A epoxy vinyl ester resins.

The Vipel F085 series is well suited for use in the field of chlorine-alkali electrolysis. Refer to AOC's "Corrosion Resistant Resin Guide" for corrosion resistance information or for questions regarding suitability of a resin to any particular chemical environment contact AOC.

Mechanical Properties

The Vipel F085 series is suitable for moldings that are subjected to particularly high static and dynamic loads. It is resistant to internal stress cracking under high loading.

Versatile

Suitable for various fabricating methods such as hand lay-up, filament winding, etc.

General Information					
Features	Acid Resistant				
	Base Resistant				
	Good Chemical Resistance				
	Good Corrosion Resistance				
	High Heat Resistance				
	Oxidation Resistant				
	Solvent Resistant				
Uses	Filaments				
Forms	Liquid				
Processing Method	Filament Winding				
	Hand Lay-up				
Physical	Nominal Value	Unit	Test Method		
Specific Gravity	1.07	g/cm³			
Styrene Content	38	%			
Exotherm					
Gel to Peak	6.0	min			
Peak	204	°C			
Gel Time (25°C) ¹	12.0	min			
Hardness	Nominal Value	Unit	Test Method		
Barcol Hardness	44		ASTM D2583		
Mechanical	Nominal Value	Unit	Test Method		
Tensile Modulus	3720	MPa	ASTM D638		

Tensile Strength (Yield)77.2MPaASTM D638Tensile Elongation (Break)3.3%ASTM D638Flexural Modulus3720MPaASTM D790Flexural Strength148MPaMTD 790ThermalNominal ValueUnitTest MethodDeflection Temperature Under Load (1.8) MPa, Unannealed)149°CASTM D648ThermosetNominal ValueUnitUnitThermoset Mix Viscosity ² (25°C)200cPUnitNOTEUnitUnitUnit1.Gel time with 0.3% cobalt 6%, 0.05% DMA and 1.5% MEKPSind Gel Strength Stre				
Flexural Modulus3720MPaASTM D790Flexural Strength148MPaASTM D790ThermalNominal ValueUnitTest MethodDeflection Temperature Under Load (1.8 MPa, Unannealed)149°CASTM D648ThermosetNominal ValueUnitTest MethodThermoset Mix Viscosity ² (25°C)200cPTermosetNOTES6l time with 0.3% cobalt 6%, 0.05% DMA and 1.5% MEKPScobalt 6%, 0.05% DMA and 1.5% MEKPScobalt 6%, Unit	Tensile Strength (Yield)	77.2	MPa	ASTM D638
Flexural Strength148MPaASTM D790ThermalNominal ValueUnitTest MethodDeflection Temperature Under Load (1.8 MPa, Unannealed)149°CASTM D648ThermosetNominal ValueUnitTest Mix D648Thermoset Mix Viscosity ² (25°C)200cPCNOTEGel time with 0.3% cobalt 6%, 0.05% DMA and 1.5% MEKPSTM D6481.Brookfield RV viscosity spindle 2 atSTM D648	Tensile Elongation (Break)	3.3	%	ASTM D638
Thermal Nominal Value Unit Test Method Deflection Temperature Under Load (1.8 MPa, Unannealed) 149 °C ASTM D648 Thermoset Nominal Value Unit Impose Thermoset Mix Viscosity ² (25°C) 200 cP Impose NOTE Enter With 0.3% cobalt 6%, 0.05% DMA and 1.5% MEKP Impose Instructure Instr	Flexural Modulus	3720	MPa	ASTM D790
Deflection Temperature Under Load (1.8 MPa, Unannealed)149°CASTM D648ThermosetNominal ValueUnitThermoset Mix Viscosity ² (25°C)200cPNOTESel time with 0.3% cobalt 6%, 0.05% DMA and 1.5% MEKPSel time with 0.3% cobalt 6%, 0.05% DMA and 1.5% MEKP1.Brookfield RV viscosity spindle 2 at	Flexural Strength	148	MPa	ASTM D790
MPa, Unannealed)149°CASTM D648ThermosetNominal ValueUnitThermoset Mix Viscosity ² (25°C)200cPNOTEGel time with 0.3% cobalt 6%, 0.05% DMA and 1.5% MEKP1.Gel time with 0.3% cobalt 6%, 0.05% DMA and 1.5% MEKPSecond time with 0.3% cobalt 6%, 0.05% DMA and 1.5% MEKP	Thermal	Nominal Value	Unit	Test Method
Thermoset Mix Viscosity ² (25°C) 200 cP NOTE Gel time with 0.3% cobalt 6%, 0.05% DMA and 1.5% MEKP Gel time with 0.3% cobalt 6%, 0.05% DMA and 1.5% MEKP 1. Brookfield RV viscosity spindle 2 at Gel time with 0.3% cobalt 6%, 0.05% DMA and 1.5% MEKP	-	149	°C	ASTM D648
NOTE Gel time with 0.3% cobalt 6%, 1. 0.05% DMA and 1.5% MEKP Brookfield RV viscosity spindle 2 at	Thermoset	Nominal Value	Unit	
Gel time with 0.3% cobalt 6%, 1. 0.05% DMA and 1.5% MEKP Brookfield RV viscosity spindle 2 at	Thermoset Mix Viscosity ² (25°C)	200	cP	
1. 0.05% DMA and 1.5% MEKP Brookfield RV viscosity spindle 2 at	NOTE			
	1.			
	2.	• •		

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

Recommended distributors for this material

Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533

Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

