LUVOCOM® 1-9051/LGF/BK

Polyamide 66

Lehmann & Voss & Co.

Message:

LUVOCOM®1-9051/LGF/BK is a polyamide 66 (nylon 66) material, which contains a glass fiber reinforced material. This product is available in Europe. LUVOCOM®The main characteristics of 1-9051/LGF/BK are: Good dimensional stability Good stiffness heat stabilizer Typical application areas include: engineering/industrial accessories Electrical/electronic applications textile/fiber Automotive Industry business/office supplies

General Information					
Filler / Reinforcement	Glass fiber reinforced material				
Additive	heat stabilizer				
Features	Good dimensional stability				
	Rigid, good				
	Good strength				
	Thermal Stability				
Uses	Gear				
	Textile applications				
	Engineering accessories				
	Switch				
	Application in Automobile Field				
	Business equipment				
	Bearing				
Appearance	Black				
Forms	Particle				
Physical	Nominal Value	Unit	Test Method		
Density	1.61	g/cm³	ISO 1183		
Molding Shrinkage	0.10 - 0.30	%	DIN 16901		
Water Absorption (23°C, 24 hr)	< 1.0	%			
Mechanical	Nominal Value	Unit	Test Method		
Tensile Modulus	18000	MPa	ISO 527-2		
Tensile Stress (Break)	270	MPa	ISO 527-2		
Tensile Strain (Yield)	2.2	%	ISO 527-2		
Flexural Modulus	14800	MPa	ISO 178		

Flexural Stress	415	MPa	ISO 178
Flexural Strain at Flexural Strength	3.3	%	ISO 178
Maximum operating temperature-Short Term	160	°C	
Insulation Resistance	> 1.0E+12	ohms	IEC 60167
Impact	Nominal Value	Unit	Test Method
Charpy Notched Impact Strength (23°C)	32	kJ/m²	ISO 179/1eA
Charpy Unnotched Impact Strength (23°C)	80	kJ/m²	ISO 179/1eU
Thermal	Nominal Value	Unit	Test Method
Continuous Use Temperature	120	°C	UL 746B
Vicat Softening Temperature	255	°C	ISO 306/A
CLTE - Flow	2.0E-5	cm/cm/°C	DIN 53752
Thermal Conductivity ¹	0.30	W/m/K	
Electrical	Nominal Value	Unit	Test Method
Surface Resistivity	> 1.0E+12	ohms	IEC 60093
Injection	Nominal Value	Unit	
Drying Temperature			
Hot air dryer, A	75.0	°C	
Hot air dryer, A Vacuum dryer, B	75.0	°C °C	
Vacuum dryer, B			
Vacuum dryer, B			
Vacuum dryer, B Drying Time	105	°C	
Vacuum dryer, B Drying Time Hot air dryer, A Vacuum dryer, B	105 6.0 - 16	°C	
Vacuum dryer, B Drying Time Hot air dryer, A Vacuum dryer, B Suggested Max Moisture	105 6.0 - 16 4.0 - 6.0	°C hr hr	
Vacuum dryer, B Drying Time Hot air dryer, A Vacuum dryer, B Suggested Max Moisture Rear Temperature	105 6.0 - 16 4.0 - 6.0 0.10	°C hr hr %	
Vacuum dryer, B Drying Time Hot air dryer, A Vacuum dryer, B Suggested Max Moisture Rear Temperature Middle Temperature	105 6.0 - 16 4.0 - 6.0 0.10 290 - 310	°C hr hr % °C	
Vacuum dryer, B Drying Time Hot air dryer, A	105 6.0 - 16 4.0 - 6.0 0.10 290 - 310 290 - 310	°C hr hr % °C °C	
Vacuum dryer, B Drying Time Hot air dryer, A Vacuum dryer, B Suggested Max Moisture Rear Temperature Middle Temperature Front Temperature	105 6.0 - 16 4.0 - 6.0 0.10 290 - 310 290 - 310 290 - 310	°C hr hr % °C °C °C	

General

In general LUVOCOM® can be processed on conventional injection moulding machines while observing the usual technical guidelines.

Any added fibrous materials or fillers may have an abrasive effect. In this case the cylinder and screw should be protected against wear as is usual in the processing of reinforced thermoplastic materials.

Lengthy dwell times for the melts in the cylinder should be avoided.

Lower the temperatures during interruptions!

Predrying (optional)

It is advisable to predry the granulate with a suitable dryer immediately before processing.

The granulate may absorb moisture from the air.

Delivery Form & Storage

Unless indicated otherwise, the material is delivered as 3mm-long pellets in sealed bags on pallets.

Preferably storage should be effected in dry and normally temperatured rooms

Additional Information

During processing the moisture level should not exceed 0.1%, otherwise molecular degradation and surface defects (e.g. smearing) may occur. Due to rapid absorption of water, originally sealed containers should only be opened immediately prior to processing. Excessively high predrying temperatures may cause discoloration.

The processing notes provided merely represent a recommendation for general use. Due to the large variety of machines, geometries and volumes of parts, etc., it may be necessary to employ different settings according to the specific application.

Please contact us for further information.

NOTE

1.

Hot-Disk, 60x60x3 mm

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

Recommended distributors for this material

Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533

Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

