Sarlink® TPE ML-1150N NAT (PRELIMINARY DATA)

Thermoplastic Elastomer

Teknor Apex Company

Message:

Sarlink ML-1100 is a general purpose thermoplastic elastomer series, available in NAT and BLK designed for automotive interior applications. Sarlink ML-1150N NAT is a medium hardness, high density, filled grade suitable for injection molding.

General Information			
Features	Sunlight Resistant		
	High specific gravity		
	High density		
	Good formability		
	Good flexibility		
	Good tear strength		
	Good coloring		
	Good adhesion		
	Low liquidity		
	Good chemical resistance		
	Good toughness		
	Fill		
	Elastic		
	Medium hardness		
Uses	Washer		
	Application in Automobile Fie	eld	
	Car interior parts		
	Soft touch application		
	Soft handle		
	General		
	Rubber substitution		
	Knob		
RoHS Compliance	RoHS compliance		
Appearance	Natural color		
Forms	Particle		
Processing Method	Injection molding		
Physical	Nominal Value	Unit	Test Method
Density	1.19	g/cm³	ISO 1183

Melt Mass-Flow Rate (MFR) (190°C/2.16 kg)	6.0	g/10 min	ASTM D1238
Hardness	Nominal Value	Unit	Test Method
Durometer Hardness			ISO 868
Shore A, 1 second, injection molding	53		ISO 868
Shore A, 5 seconds, injection molding	51		ISO 868
Shore A, 15 seconds, injection molding	49		ISO 868
Elastomers	Nominal Value	Unit	Test Method
Tensile Stress ¹			ISO 37
Transverse flow: 100% strain	1.13	MPa	ISO 37
Flow: 100% strain	1.60	MPa	ISO 37
Tensile Stress ²			ISO 37
Transverse flow: Fracture	4.90	MPa	ISO 37
Flow: Fracture	4.30	MPa	ISO 37
Tensile Elongation ³			ISO 37
Transverse flow: Fracture	860	%	ISO 37
Flow: Fracture	740	%	ISO 37
Tear Strength ⁴			ISO 34-1
Transverse flow	20	kN/m	ISO 34-1
Flow	20	kN/m	ISO 34-1
Compression Set ⁵			ISO 815
23°C, 22 hr	25	%	ISO 815
70°C, 22 hr	43	%	ISO 815
90°C, 70 hr	69	%	ISO 815
125°C, 70 hr	93	%	ISO 815
Aging	Nominal Value	Unit	Test Method
Change in Tensile Strength in Air ⁶			ISO 188
Transverse flow: 110°C, 1008 hr	8.2	%	ISO 188
Flow: 110°C, 1008 hr	14	%	ISO 188
Transverse flow: 100% strain 110°C, 1008 hr	2.7	%	ISO 188
Flow: 100% strain 110°C, 1008 hr	3.8	%	ISO 188
Transverse flow: 125°C, 168 hr	12	%	ISO 188
Flow: 125°C, 168 hr	14	%	ISO 188
Transverse flow: 100% strain 125°C, 168 hr	-0.88	%	ISO 188
Flow: 100% strain 125°C, 168 hr	13	%	ISO 188
Change in Tensile Strain at Break in Air ⁷			ISO 188
Transverse flow: 110°C, 1008 hr	8.1	%	ISO 188
Flow: 110°C, 1008 hr	12	%	ISO 188
Transverse flow: 125°C, 168 hr	15	%	ISO 188
Flow: 125°C, 168 hr	18	%	ISO 188

ISO 188 ISO 188 ISO 188 Test Method
ISO 188
ISO 188
100.100
ISO 188
ISO 188
ISO 188
-

The information and recommendations contained in this bulletin are, to the best of our knowledge, accurate and reliable but no guarantee of their accuracy is made. All products are sold upon condition that purchasers shall make their own tests to determine the suitability of such products for their particular purposes and uses and purchaser assumes all risks and liability for the results of use of the products, including use in accordance with seller's recommendations. Nothing in this bulletin constitutes permission or a recommendation to practice or use any invention covered by any patent owned by this company or others. There is no warranty of merchantability and there are no other warranties for the products described. For detailed Product Stewardship information, please contact us. Any product of Teknor Apex, including product names, shall not be used or tested in medical or food contact applications without the prior written acknowledgement of Teknor Apex as to the intended use. Please note that some products may not be available in one or more countries.

Injection	Nominal Value	Unit
Rear Temperature	171 - 193	°C
Middle Temperature	177 - 199	°C
Front Temperature	182 - 204	°C
Nozzle Temperature	188 - 210	°C
Processing (Melt) Temp	188 - 210	°C
Mold Temperature	25 - 66	°C
Injection Pressure	1.38 - 6.89	MPa
Injection Rate	Moderate-Fast	
Back Pressure	0.172 - 0.345	MPa
Screw Speed	50 - 100	rpm
Cushion	3.81 - 25.4	mm
Intention instructions		

Injection instructions

Drying is not necessary. However, if moisture is a problem, dry the pellets for 2 to 4 hours at 150°F (65°C).

NOTE	
1.	Type 1, 510mm/min
2.	Type 1, 510mm/min
3.	Type 1, 510mm/min
4.	B method, right angle specimen (without cut), 510mm/min
5.	Туре а
6.	Type 1
7.	Type 1
8.	15 sec
9.	5 sec
10.	1 sec
11.	15 sec
12.	5 sec

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

Recommended distributors for this material

Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533

Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

