

STERalloy™ FDG 2766-5

Thermoplastic

Hapco Inc.

Message:

STERalloy FDG is the first Liquid Molding Polymer Alloy Series that has been specifically designed for food and drug applications. All of products in the STERalloy FDG Series exhibit unique physical and chemical properties and have been used in numerous applications where biocompatibility is required.

Key Advantages:

- Approvable Materials
- Wide range of hardnesses
- ROHS compliant
- Very high physical properties
- Low moisture sensitivity
- Easy to use

The food, drug, pharmaceutical, wine, beer, juice, dairy, hospital equipment, and prosthetic industries are just some examples of applications that utilize special products such as STERalloy FDG.

STERalloy FDG Elastomeric Series:

- various hardness elastomers, shore 20A - 72D
- clear in color
- available in 2 speeds - fast and slow

STERalloy FDG Rigid Series:

- rigid, tough polymer alloy plastics
- high heat distortion
- high physical properties

| General Information | | | |
|------------------------------|---------------------------------|-------------------|-------------|
| Features | Food Contact Acceptable | | |
| | Good Processability | | |
| Uses | Filtration Media | | |
| | Food Containers | | |
| | Medical/Healthcare Applications | | |
| | Non-specific Food Applications | | |
| | Pharmaceuticals | | |
| | Prosthetics | | |
| RoHS Compliance | RoHS Compliant | | |
| Appearance | Clear/Transparent | | |
| Forms | Liquid | | |
| Physical | Nominal Value | Unit | Test Method |
| Specific Gravity | 1.04 | g/cm ³ | ASTM D4669 |
| Molding Shrinkage - Flow | 0.10 to 0.25 | % | ASTM D2566 |
| Weight - per cubic inch | 17 | g | |
| Gel Time ¹ (25°C) | 5.0 | min | ASTM D2971 |
| Hardness | Nominal Value | Unit | Test Method |
| Durometer Hardness (Shore A) | 65 | | ASTM D2240 |
| Mechanical | Nominal Value | Unit | Test Method |

| | | | |
|--------------------------------|--|------|-----------------|
| Tensile Strength | 5.52 | MPa | ASTM D638 |
| Tensile Elongation (Break) | 950 | % | ASTM D638 |
| Elastomers | Nominal Value | Unit | Test Method |
| Tear Strength ² | 29.8 | kN/m | ASTM D624 |
| Impact | Nominal Value | Unit | Test Method |
| Notched Izod Impact | No Break | | ASTM D256 |
| Unnotched Izod Impact | No Break | | ASTM D256 |
| Thermoset | Nominal Value | Unit | Test Method |
| Thermoset Components | | | |
| Part A | Mix Ratio by Weight: 100, Mix Ratio by Volume: 100 | | |
| Part B | Mix Ratio by Weight: 20, Mix Ratio by Volume: 20 | | |
| Thermoset Mix Viscosity (25°C) | 4000 | cP | ASTM D4878 |
| Demold Time (21°C) | 120 to 240 | min | Internal Method |
| NOTE | | | |
| 1. | 100 g | | |
| 2. | Die C | | |

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

Recommended distributors for this material

Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533

Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

