Medalist® MD-50288

Thermoplastic Elastomer

Teknor Apex Company

Message:

This compound is intended for use in medical and healthcare applications, particularly for extruded medical tubing.

General Information					
Features	High purity				
	Pressure cooker disinfection				
	Ethylene oxide disinfection				
	Anti-gamma radiation				
	Good processing stability				
	Kink resistance				
	Definition, high				
	No kinetic components				
Uses	Drug				
	Medical/nursing supplies				
Agency Ratings	ISO 10993 Part 5				
	ISO 13485				
Appearance	Clear/transparent				
Forms	Particle				
Processing Method	Extrusion				
	Injection molding				
Physical	Nominal Value	Unit	Test Method		
Specific Gravity	0.888	g/cm³	ASTM D792		
Melt Mass-Flow Rate (MFR) (200°C/5.0 kg)	8.0	g/10 min	ASTM D1238		
Hardness	Nominal Value	Unit	Test Method		
Durometer Hardness			ASTM D2240		
Shaw A, 1 sec	91		ASTM D2240		
Shaw A, 5 seconds	89		ASTM D2240		
Elastomers	Nominal Value	Unit	Test Method		
Tensile Stress			ASTM D412		
50% strain	7.41	MPa	ASTM D412		
100% strain	7.34	МРа	ASTM D412		
300% strain	8.69	МРа	ASTM D412		
Tensile Strength (Break)	15.6	MPa	ASTM D412		

Tensile Elongation (Break)	610	%	ASTM D412
Tear Strength	80.6	kN/m	ASTM D624
Compression Set			ASTM D395
23°C, 22 hr	29	%	ASTM D395
70°C, 22 hr	85	%	ASTM D395
Legal statement			

The information and recommendations contained in this bulletin are, to the best of our knowledge, accurate and reliable but no guarantee of their accuracy is made. All products are sold upon condition that purchasers shall make their own tests to determine the suitability of such products for their particular purposes and uses and purchaser assumes all risks and liability for the results of use of the products, including use in accordance with seller's recommendations. Nothing in this bulletin constitutes permission or a recommendation to practice or use any invention covered by any patent owned by this company or others. There is no warranty of merchantability and there are no other warranties for the products described. For detailed Product Stewardship information, please contact us. Any product of Teknor Apex, including product names, shall not be used or tested in medical or food contact applications without the prior written acknowledgement of Teknor Apex as to the intended use. Please note that some products may not be available in one or more countries.

Injection	Nominal Value	Unit	
Rear Temperature	149 - 171	°C	
Middle Temperature	171 - 193	°C	
Front Temperature	193 - 227	°C	
Nozzle Temperature	193 - 227	°C	
Processing (Melt) Temp	193 - 227	°C	
Mold Temperature	21.1 - 51.7	°C	
Back Pressure	0.345 - 1.03	МРа	
Screw Speed	50 - 100	rpm	
Cushion	3.56 - 25.4	mm	
Injection instructions			

Drying is not necessary. However, if moisture is a problem, dry the pellets for 2 to 4 hours at 150°F (65°C).

Extrusion	Nominal Value	Unit
Cylinder Zone 1 Temp.	171 - 188	°C
Cylinder Zone 2 Temp.	182 - 196	°C
Cylinder Zone 3 Temp.	185 - 204	°C
Cylinder Zone 5 Temp.	204 - 227	°C
Die Temperature	204 - 227	°C
Extrusion instructions		

Screw Speed: 30 to 100 rpm.Screen Pack Recommendation:60/200/200/60 to 60/200/400/400/200/60 mesh size.

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

Recommended distributors for this material

Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533 Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

