

Vipel® F010-BNT-00

Vinyl Ester

AOC, L.L.C.

Message:

Vipel Corrosion Resistant Bisphenol A, Epoxy Vinyl Ester Resins

AOC's Vipel F010 series is a bisphenol A epoxy-based vinyl ester resin dissolved in styrene. The Vipel F010 series is ideally suited for use in hand lay-up, sprayup, filament winding, SMC, and pultrusion processes where outstanding mechanical properties and excellent resistance to chemicals and heat are required.

Versatile

Wide formulating capabilities allow for use in many processes and for optimization of cost/performance. Unique composition produces a tough and versatile resin with excellent crack and craze resistance in molded parts. Vipel F010 is suitable for moldings that are subjected to particularly high static or dynamic loads, such as pipe, tanks, duct work and flooring applications. Vinyl ester resins have excellent resistance to sustained heat.

Corrosion Resistant

Vipel F010 highly resistant to hydrogen peroxide, and alkalis, and performs well in various stages of hypochlorite and chlorine production. Refer to AOC's "Corrosion Resistant Resin Guide" for corrosion resistance information or for questions regarding suitability of a resin to any particular chemical environment contact AOC.

Food and Drug

All resins in this datasheet are manufactured from raw materials that are listed in FDA regulation Title 21 CFR 177.2420. It is the fabricator's responsibility to also be sure that the final composite is well cured. All composites used for FDA applications should be post cured at 180°F/82°C for at least 4 hours. After post curing it should be washed with soap and water and rinsed.

General Information			
Features	Alkali Resistant		
	Food Contact Acceptable		
	Good Corrosion Resistance		
	High Heat Resistance		
Uses	Flooring Maintenance/Repair		
	Piping		
	Plumbing Parts		
	Tanks		
Agency Ratings	FDA 21 CFR 177.2420		
Forms	Liquid		
Processing Method	Filament Winding		
	Hand Lay-up		
	Pultrusion		
	Spraying		
Physical	Nominal Value	Unit	Test Method
Specific Gravity	1.10	g/cm ³	
Styrene Content	27	%	
Exotherm			
Gel to Peak	10.0	min	

Peak	166	°C	
Gel Time (25°C) ¹	17.0	min	
Critical Strain Energy	100	J/m ²	ASTM E399
Stress Intensity Factor	0.600		ASTM E399
Hardness	Nominal Value	Unit	Test Method
Barcol Hardness	39		ASTM D2583
Mechanical	Nominal Value	Unit	Test Method
Tensile Modulus	3170	MPa	ASTM D638
Tensile Strength (Yield)	88.3	MPa	ASTM D638
Tensile Elongation (Break)	6.2	%	ASTM D638
Flexural Modulus	3450	MPa	ASTM D790
Flexural Strength	152	MPa	ASTM D790
Thermal	Nominal Value	Unit	Test Method
Deflection Temperature Under Load (1.8 MPa, Unannealed)	120	°C	ASTM D648
Glass Transition Temperature	130	°C	DIN 53445
Electrical	Nominal Value	Unit	Test Method
Surface Resistivity	> 1.0E+13	ohms	DIN 53482
Volume Resistivity ²	> 1.0E+16	ohms · cm	DIN 53482
Electric Strength (0.700 mm)	120	kV/mm	DIN 53481
Dielectric Constant			DIN 53483
60 Hz ³	3.50		
60 Hz ⁴	3.40		
1 kHz ⁵	3.50		
1 kHz ⁶	3.40		
1 MHz ⁷	3.40		
1 MHz ⁸	3.30		
Dissipation Factor			DIN 53483
60 Hz ⁹	3.7E-3		
60 Hz ¹⁰	2.5E-3		
1 kHz ¹¹	3.3E-3		
1 kHz ¹²	2.2E-3		
1 MHz ¹³	2.3E-3		
1 MHz ¹⁴	1.6E-3		
Thermoset	Nominal Value	Unit	Test Method
Thermoset Mix Viscosity ¹⁵ (25°C)	3200	cP	
Post Cure Time (82°C)	4.0	hr	
NOTE			
1.	Gel time with 0.25% cobalt 6% and 1.25% MEKP		
2.	after 24 hrs in drinking water		
3.	after 24 hrs in drinking water		
4.	Dry		

5.	after 24 hrs in drinking water
6.	Dry
7.	after 24 hrs in drinking water
8.	Dry
9.	after 24 hrs in drinking water
10.	Dry
11.	after 24 hrs in drinking water
12.	Dry
13.	after 24 hrs in drinking water
14.	Dry
15.	Brookfield RV viscosity spindle 3 at 20 rpm

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

Recommended distributors for this material

Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533

Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

