Quadrathane™ ARC-75A-B20

Thermoplastic Polyurethane Elastomer (PC Based)

Biomerics, LLC

Message:

Quadrathane[™] ARC-75A-B20 is high performance aromatic polycarbonate thermoplastic polyurethane. The polymer is loaded with 20% barium sulfate, naturally white and supplied in small pellets for ease of processing. The material exhibits excellent mechanical properties, oxidative stability, biocompatibility, superior biostability in long term implantable devices, high resiliency, and chemical resistance. The resin has consistent melt flow properties making it ideal for extrusion.

Quadrathane™, Quadraflex™, Quadraban™ and Quadraplast™ performance polymers are primarily used in life science and medical applications including vascular access devices, surgical supplies, respiratory devices, tracheotomy devices, and other medical applications. Typical end products include tubing, catheter parts, balloons, and various medical device components. These performance polymers are available in a variety of durometers, radiopacifiers, colors, and custom formulations.

General Information					
Filler / Reinforcement	Barium sulfate, 20% filler by weight				
Features	Aroma				
	Antioxidation				
	Workability, good				
	Good liquidity				
	Good chemical resistance				
	Biocompatibility				
	Elastic				
	Resistance				
Uses	Pipe fittings				
	Human implant				
	Surgical instruments				
	Medical/nursing supplies				
	Mil 's				
Appearance	White				
Forms	Particle				
Processing Method	Extrusion				
	Injection molding				
Physical	Nominal Value	Unit	Test Method		
Specific Gravity	1.33	g/cm³	ASTM D792		
Melt Mass-Flow Rate (MFR) (190°C/2.16					
kg)	7.5	g/10 min	ASTM D1238		
Molding Shrinkage - Flow	0.80 - 1.3	%	ASTM D955		
Hardness	Nominal Value	Unit	Test Method		
Durometer Hardness (Shore A)	75		ASTM D2240		
Mechanical	Nominal Value	Unit	Test Method		
Flexural Modulus	5.52	МРа	ASTM D790		

Elastomers	Nominal Value	Unit	Test Method
Tensile Stress (10% Strain)	2.76	MPa	ASTM D412
Tensile Stress			ASTM D412
100% strain	4.65	MPa	ASTM D412
300% strain	8.96	MPa	ASTM D412
Tensile Strength (Break)	34.5	MPa	ASTM D412
Tensile Elongation (Break)	530	%	ASTM D412
Thermoset	Nominal Value	Unit	
Post Cure Time (38°C)	6.0 - 10	hr	
Injection	Nominal Value	Unit	
Drying Temperature	54.4	°C	
Drying Time	4.0	hr	
Suggested Max Moisture	< 3.0E-3	%	
Rear Temperature	177	°C	
Front Temperature	191	°C	
Nozzle Temperature	196	°C	
Processing (Melt) Temp	204	°C	
Mold Temperature	4.44 - 32.2	°C	
Injection Rate	Slow		
Screw Compression Ratio	2.5:1.0 - 3.5:1.0		
Injection instructions			
Injection Speed: 10 g/secCooling/Ho	old Time: Long, at least 50% of cycle (20 to 60 secs depending on thickn	ess)
Extrusion	Nominal Value	Unit	
Drying Temperature	54.4	°C	
Drying Time	4.0	hr	
Suggested Max Moisture	< 0.030	%	
Cylinder Zone 1 Temp.	171	°C	
Cylinder Zone 2 Temp.	182	°C	
Cylinder Zone 3 Temp.	188	°C	
Cylinder Zone 4 Temp.	193	°C	
Melt Temperature	193	°C	
Die Temperature	193 - 216	°C	
Back Pressure	6.89 - 12.4	MPa	

Screen Pack: 250 meshScrew Speed: Low sheer, 150 to 250 rpmWater Bath: 80 to 110°F

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

Recommended distributors for this material

Extrusion instructions

Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533

Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

