# LUVOCOM® 1105-8135/VI

### Polyetheretherketone

#### Lehmann & Voss & Co.

#### Message:

LUVOCOM®1105-8135/VI is a polyetheretherketone (PEEK) material. This product is available in North America, Africa and the Middle East, Latin America, Europe or Asia Pacific. LUVOCOM®The main features of 1105-8135/VI are: flame retardant/rated flame Flame Retardant sterilizable chemical resistance Typical application areas include: textile/fiber engineering/industrial accessories Aerospace Automotive Industry medical/health care

General Information			
Features	Good liquidity		
	Good chemical resistance		
	Hydrolysis resistance		
	Disinfect with steam		
	Flame retardancy		
Uses	Textile applications		
	Engineering accessories		
	Aerospace applications		
	Application in Automobile Field		
	Medical/nursing supplies		
Appearance	Violet		
Physical	Nominal Value	Unit	Test Method
Density	1.31	g/cm³	ISO 1183
Molding Shrinkage	1.0 - 1.6	%	DIN 16901
Water Absorption (23°C, 24 hr)	< 0.50	%	
Mechanical	Nominal Value	Unit	Test Method
Tensile Modulus	4000	MPa	ISO 527-2
Tensile Stress (Break)	100	MPa	ISO 527-2
Tensile Strain (Yield)	4.5	%	ISO 527-2
Flexural Modulus	3000	MPa	ISO 178
Flexural Stress	140	MPa	ISO 178

%

ISO 178

6.0

Flexural Strain at Flexural Strength

°C ohms e Unit kJ/m <sup>2</sup> e Unit e Unit e Unit	Test Method 1 <sup>2</sup> ISO 179/1eA 1 <sup>2</sup> ISO 179/1fU Test Method UL 746B Test Method UL 94	Ą J d
e Unit kJ/m <sup>2</sup> kJ/m <sup>2</sup> e Unit e Unit e Unit	Test Method 1 <sup>2</sup> ISO 179/1eA 1 <sup>2</sup> ISO 179/1fU Test Method UL 746B Test Method UL 94	Ą J d
e Unit kJ/m <sup>2</sup> kJ/m <sup>2</sup> e Unit e Unit e Unit	Test Method 1 <sup>2</sup> ISO 179/1eA 1 <sup>2</sup> ISO 179/1fU Test Method UL 746B Test Method UL 94	Ą J d
kJ/m <sup>2</sup> kJ/m <sup>2</sup> e Unit °C e Unit	n <sup>2</sup> ISO 179/1eA n <sup>2</sup> ISO 179/1fU Test Method UL 746B Test Method UL 94	Ą J d
kJ/m <sup>2</sup> e Unit °C e Unit e Unit	1 <sup>2</sup> ISO 179/1fU Test Method UL 746B Test Method UL 94	J d
e Unit °C e Unit e Unit	Test Method UL 746B Test Method UL 94	d
e Unit	UL 746B Test Method UL 94	-
e Unit e Unit	Test Method UL 94	d
e Unit	UL 94	d
°C		
°C		
C		
°C		
hr		
hr		
%		
°C		
	°C °C °C	°C ℃

#### General

In general LUVOCOM® can be processed on conventional injection moulding machines while observing the usual technical guidelines.

Any added fibrous materials or fillers may have an abrasive effect. In this case the cylinder and screw should be protected against wear as is usual in the processing of reinforced thermoplastic materials.

Lengthy dwell times for the melts in the cylinder should be avoided.

Lower the temperatures during interruptions!

Predrying (optional)

It is advisable to predry the granulate with a suitable dryer immediately before processing.

The granulate may absorb moisture from the air.

Delivery Form & Storage

Unless indicated otherwise, the material is delivered as 3mm-long pellets in sealed bags on pallets.

Preferably storage should be effected in dry and normally temperatured rooms

Additional Information

During processing, the moisture content should not exceed 0.05%. To avoid internal stresses, a medium to high injection rate should be used. An increase in tool temperature may be helpful. Post-crystallization may lead to warpage at elevated operating temperatures. This can be counteracted by suitable heat treatment.

The processing notes provided merely represent a recommendation for general use. Due to the large variety of machines, geometries and volumes of parts, etc., it may be necessary to employ different settings according to the specific application.

High-temperature polymers place increased demands on the tool steels employed.

Please contact us for further information.

NOTE

1.

Not recognized by UL.

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any

#### Recommended distributors for this material

## Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533

Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

