LUVOCOM® 1/CF/7/GK/15/BK

Polyamide 66

LEHVOSS Group

Message:

LUVOCOM® 1/CF/7/GK/15/BK is a polyamide 66 (nylon 66) material, which contains 15% glass beads and 7.0% carbon fiber reinforced materials. This product is available in North America, Africa and the Middle East, Latin America, Europe or Asia Pacific. LUVOCOM® The main features of 1/CF/7/GK/15/BK are: Conductivity anti-warping Typical application areas include: engineering/industrial accessories textile/fiber Automotive Industry business/office supplies

General Information					
Filler / Reinforcement	Glass beads, 15% filler by weight				
	Carbon fiber reinforced material, 7.0% filler by weight				
Features	Conductivity				
	Low warpage				
	Static conduction				
Uses	Gear	Gear			
	Textile applications				
	Engineering accessories				
	Application in Automobile Field				
	Business equipment				
	Cam				
Appearance	Black				
Physical	Nominal Value	Unit	Test Method		
Density	1.28	g/cm³	ISO 1183		
Molding Shrinkage	0.40 - 0.70	%	DIN 16901		
Water Absorption (23°C, 24 hr)	< 1.0	%			
Mechanical	Nominal Value	Unit	Test Method		
Tensile Modulus	8000	MPa	ISO 527-2		
Tensile Stress (Break)	135	MPa	ISO 527-2		
Tensile Strain (Yield)	3.0	%	ISO 527-2		
Flexural Modulus	7000	MPa	ISO 178		
Flexural Stress	200	MPa	ISO 178		
Flexural Strain at Flexural Strength	4.0	%	ISO 178		

Maximum operating temperature-Short			
Term	150	°C	
Insulation Resistance		ohms	IEC 60167
Impact	Nominal Value	Unit	Test Method
Charpy Unnotched Impact Strength (23°C)	40	kJ/m²	ISO 179/1fU
Thermal	Nominal Value	Unit	Test Method
Continuous Use Temperature	90.0	°C	UL 746B
Vicat Softening Temperature	250	°C	ISO 306/A
CLTE - Flow	4.0E-5	cm/cm/°C	DIN 53752
Thermal Conductivity	0.30	W/m/K	DIN 52612
Electrical	Nominal Value	Unit	Test Method
Surface Resistivity	< 1.0E+6	ohms	IEC 60093
Injection	Nominal Value	Unit	
Drying Temperature			
Hot air dryer, A	75	°C	
Vacuum dryer, B	105	°C	
Drying Time			
Hot air dryer, A	6.0 - 16	hr	
Vacuum dryer, B	4.0 - 6.0	hr	
Rear Temperature	290 - 310	°C	
Middle Temperature	290 - 310	°C	
Front Temperature	290 - 310	°C	
Nozzle Temperature	280 - 300	°C	
Processing (Melt) Temp	290	°C	
Mold Temperature	90 - 120	°C	
Injection instructions			

General

In general LUVOCOM® can be processed on conventional injection moulding machines while observing the usual technical guidelines.

Any added fibrous materials or fillers may have an abrasive effect. In this case the cylinder and screw should be protected against wear as is usual in the processing of reinforced thermoplastic materials.

Lengthy dwell times for the melts in the cylinder should be avoided.

Lower the temperatures during interruptions!

Predrying (optional)

It is advisable to predry the granulate with a suitable dryer immediately before processing.

The granulate may absorb moisture from the air.

Delivery Form & Storage

Unless indicated otherwise, the material is delivered as 3mm-long pellets in sealed bags on pallets.

Preferably storage should be effected in dry and normally temperatured rooms

Additional Information

During processing the moisture level should not exceed 0.1%, otherwise molecular degradation and surface defects (e.g. smearing) may occur. Due to rapid absorption of water, originally sealed containers should only be opened immediately prior to processing. Excessively high predrying temperatures may cause discoloration.

The processing notes provided merely represent a recommendation for general use. Due to the large variety of machines, geometries and volumes of parts, etc., it may be necessary to employ different settings according to the specific application. Please contact us for further information.

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533

Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

